#### CDL066...

"40W" DC Coils	CAP. I • 74
CONNECTORS STANDARD	CAP. I • 20

#### **ORDERING CODE**

#### **ORDERING CODE**

CDL Stackable circuit selector valve

Size NG06

06

6

W

1

No. of way (single element)

Threaded connectors 3/8" BSP

I Internal drainage

No. of elements: 1/2/3/4/5

\* Voltage (Tab. 1)

Variants (Tab. 2)

Serial No.

# CDL066... STACKABLE CIRCUIT SELECTOR VALVES

The stackable circuit selector valves, type CDL.06.6, allows one single drive of 6 users with 5 elements connected in series.

As they are moved from high performances solenoids they don't need the external drainage.

This valves can manage high hydraulic powers with a minimal pressure drop.

Max. pressure 250 bar Max. flow 50 l/min Overlap negative Hydraulic fluids Mineral oils DIN 51524 Fluid viscosity  $10 \div 500 \text{ mm}^2/\text{s}$ Fluid temperature -25°C ÷ 75°C Ambient temperature -25°C ÷ 60°C Max. contamination level class 10 in accordance NAS with 1638 with filter  $\beta_{25} \ge 75$ see "Overall dimension"

#### TAB.1 - 40W COIL

#### DC VOLTAGE

L 12V M 24V

W Without DC coil

Voltage codes are not stamped on the plate, their are readable on the coils.


### Tab.2 - Variants

No variant (without connectors)	S1(*)
Viton	SV(*)
Emergency button	ES(*)
Rotary emergency button	P2(*)
Raccordements Deutsch DT04-2P	CZ


Other variants available on request.

(\*) Coils with Hirschmann connection supplied without connectors. The connectors can be ordered separately, CAP.


#### HYDRAULIC SYMBOLS



## MULTISTATION CONNECTION



# PRESSURE DROPS




P1  $\rightarrow$  C1, P1  $\rightarrow$  C2, P2  $\rightarrow$  C3 e P2  $\rightarrow$  C4

The fluid used is a mineral oil with a viscosity of 46 mm²/s at 40°C; the tests have been carried out at a fluid temperature of 40°C.

Fixing screws UNI 5931 M6x60 with material specifications min. 8.8 Tightening torque for studs 8 Nm / 0.8 Kgm Tightening torque for rods 20 Nm / 2 Kgm

#### **OVERALL DIMENSIONS**



 $(\mbox{\ensuremath{^{\star}}})$  For multiple composition rods and studs are available.

